



製品レイアウト
PRODUCT LAYOUT





基板レイアウト(参考)

PCB PATTERN LAYOUT (REFERENCE)
(参考: メタルマスク厚さ 0.10mm, マスク開口率100%)
(REFERENCE: METAL MASK THICKNESS 0.10mm, APERTURE RATIO 100%)



パターン非推奨エリア

パターンを引き回す際は、製品機能に影響がないことをご確認ください。
PATTERN IS NOT RECCOMENDED ON THE HATCHED AREA.
PLEASE CHECK NOT TO HAVE PROBLEM FOR PRODUCT FUNCTION
WHEN SETTING PATTERN ON THE HATCHED AREA.







MATED CONNECTORS

嵌合相手: 502578 シリーズ
MATE WITH: 502578 SERIES

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex					
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 742719 DRWN: MIKEDA012023/06/23 CHK'D: SAKIYAMA2023/06/23 APPR: AIDA2023/06/23 INITIAL REVISION: DRWN: MIKEDA012019/11/07 APPR: KOMURAKAMI2019/11/20				CLIK-MATE 1.5 SINGLE ROW SMT VT TYPE REC ASSY GOLD PLATING					
ANGULAR TOL ± 3.0 °												
4 PLACES		± 0.2										
3 PLACES		± 0.2										
2 PLACES		± 0.2										
1 PLACE		± 0.2	PRODUCT CUSTOMER DRAWING				DOCUMENT NUMBER 2132250000-SD			DOC TYPE PSD	DOC PART 000	REVISION F
0 PLACES		± 0.2										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
				A3-SIZE	213225			GENERAL		2 OF 6		

ロック形状および吸着エリア
LOCK SHAPE AND VACCUME AREA



SECTION X-X

12-15 極
12-15 CKTS

5.0	15
	14
	13
	12
	11
	10
	9
	8
13.6	7
12.1	6
10.6	5
9.1	4
7.6	3
6.1	2
D	極数 CKT NO

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex	
DIMENSION UNITS mm	SCALE NTS				
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 742719 DRWN: MIKEDA01 2023/06/23 CHK'D: SAKIYAMA 2023/06/23 APPR: AIDA 2023/06/23 INITIAL REVISION: DRWN: MIKEDA01 2019/11/07 APPR: KOMURAKAMI 2019/11/20		SINGLE ROW SMT VT TYPE REC ASSY GOLD PLATING	
ANGULAR TOL ± 3.0 °				PRODUCT CUSTOMER DRAWING	
4 PLACES ± 0.2				DOCUMENT NUMBER 2132250000-SD	
3 PLACES ± 0.2				DOC TYPE PSD	DOC PART 000
2 PLACES ± 0.2				REVISION F	
1 PLACE ± 0.2		MATERIAL NUMBER		SHEET NUMBER	
0 PLACES ± 0.2		CUSTOMER GENERAL		3 OF 6	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 	DRAWING A3-SIZE	SERIES 213225	

3

適用製品及び各種仕様書

APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER	DOCUMENT NUMBER
	213225 ****	2132259200-SPK

適用嵌合相手 MATE WITH	HOUSING	TERMINAL (GOLD PLATING)		
		PLATING THK	#24-28	#28-30
製品番号 PRODUCT NUMBER	502578 ****	0.1 micro-meters	213028 1*00	213029 1*00
		0.38 micro-meters	213028 3*00	213029 3*00
		0.76 micro-meters	213028 7*00	213029 7*00
製品仕様書 PRODUCT SPECIFICATION	5025780004-PS			
アプリケーション仕様書 APPLICATION SPECIFICATION	AS-502578-001			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		±	3.0 °	CLIK-MATE 1.5 SINGLE ROW SMT VT TYPE REC ASSY GOLD PLATING					
4 PLACES		±	0.2	EC NO: 742719			PRODUCT CUSTOMER DRAWING		
3 PLACES		±	0.2	DRWN: MIKEDA012023/06/23					
2 PLACES		±	0.2	CHK'D: SAKIYAMA2023/06/23					
1 PLACE		±	0.2	APPR: AIDA2023/06/23			DOCUMENT NUMBER 2132250000-SD		
0 PLACES		±	0.2	INITIAL REVISION: DRWN: MIKEDA012019/11/07 APPR: KOMURAKAMI2019/11/20					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
				A3-SIZE		213225		GENERAL	5 OF 6

