



Part Number : [1600740008](#)
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option C, with Connector Position Assurance, Dark Gray
Series Number : 160074
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[1600740008_sd.pdf](#)
[PK-31300-635-001.pdf](#)

3D Models and Design Files
[1600740008_stp.zip](#)

Specifications
[AS-33472-100-CH-001.pdf](#)
[PS-160074-0001-001.pdf](#)
[1600742276-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	160074
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option C, with Connector Position Assurance, Dark Gray
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056561679

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	20
Color - Resin	Gray (Dark)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	24.200/g
Number of Rows	2

Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	C
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>