


Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_DRAIN
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield



TOI FRANCES: ± 0.05

UGEPATAEYA

- Code: A01.
- Interface: Curled edge.
- Lifetime: 1,500 cycles.
- Material: Copper plated with nickel.
- Type: Without pillar.
- Appearance size: 14.45mm.
- Mounting method: Two-pronged fishhook SMT.
- Specification: 9 pins.
- Series: AF3.0 USB.

FIRST VIEW			
			
SCALE	1 : 1	UNIT	mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

AF3.0板上SMT鱼叉两脚 短体L=14.45 卷边

of DWG NO: UGEPa-P07003

PART NO: UGEP A1903633

MODEL NO: UGEPATAEYA

NAME:

AF3.0 USB CONN

SAMZO COMPONENTS
Electronic switch and connector manufacturer