

A51MC7-002BPH0-0000
medi_snap
type_a5




General information

Part number	A51MC7-002BPH0-0000
Termination	solder
Size	1
Locking principle	break
Coding	c_key_medi
Cable outlet	overmolding




Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.

CODING: 60°



POSITIONS: 2 Positions



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	2
Contact type	pins
Contact diameter	13mm
Insulator material	psu_gray
Wire cross section	20_awg
Termination	solder
Termination diameter	11mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	13_mm	iec_60601_2mopp_2moop
Nominal current single contact	12_a	iec_60512_5_2
Nominal current insert	12 A	vde_0298_4
Test voltage	14_kv_ac	eia_364_20f

safety_text
iec_60601_plug

Mechanical and environmental data

Degree of protection*	ip67
Operating temperature	50_120_c
Mating cycles	5000

mated

Material and surface treatments

Housing	psu_gray
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text