



EUROCARD CONNECTORS



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)

V42254B1201R960=PC612 MESSERLE

[EUROCARD](#) | [Eurocard Type R](#)

2-1393659-8

TE Internal Number: 2-1393659-8

Alias ID: V42254B1201R960

[Converted to EU RoHS/ELV Compliant](#)

Connector Style **Plug**

Applies To **Printed Circuit Board**

Connector System **Board-to-Board**

Number of Power or Coaxial Positions **2**

Centerline (mm) **2.54**

Product Drawings

[PIN ASSEMBLY EUROCARD TYPES Q AND R AND SHORT VERSIONS](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style	Plug
Applies To	Printed Circuit Board
Connector System	Board-to-Board
Row-to-Row Spacing (mm)	2.54
DIN Level	II
Product Type	Connector
PCB Mounting Orientation	Vertical
Make First / Break Last	No
Shielded	No
Guides	Without
Post Type	Solder Post
Connector Type	Connector Assembly

Configuration Features

Number of Power or Coaxial Positions	2
Number of Positions	96
Rows Loaded	A. B. C.

	Notes	PDF
Body Features	Color	Gray
Contact Features	Contact Type	Pin
	Contact Base Material	Phosphor Bronze
Termination Features	Termination Post Length	2.9 mm [.114 in]
	Interface Type	Eurocard/DIN 41612
Mechanical Attachment	Panel Mount Retention	Without
	Mating Alignment	Without
	PCB Mount Retention	With
	PCB Mount Retention Type	Mounting Holes
Housing Features	Centerline (mm)	2.54
	Housing Material	Thermoplastic PBT GF
Dimensions	Tail Length (mm)	2.9
	Height (mm)	11.51
Industry Standards	UL Flammability Rating	UL 94V-0
Packaging Features	Packaging Method	Package
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	