

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5050703422

Status:


Active

Overview:

SlimStack™ 0.35mm pitch Board-to-Board Connectors

Description:

SlimStack Board-to-Board Connector, 0.35mm Pitch, SSB RP Series, Plug, 0.60 or 0.70mm Mated Height, 2.00mm Mated Width, 34 Circuits, Armor Nail



Documents:

3D Model

Drawing (PDF)

Product Specification 5050660000-014 (PDF)

Product Specification 5050660000-A06 (PDF)

Packaging Specification 5050709200-203 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

|                                |                                                   |
|--------------------------------|---------------------------------------------------|
| General                        |                                                   |
| Product Family                 | PCB Headers                                       |
| Series                         | 505070                                            |
| Application                    | Board-to-Board                                    |
| Overview                       | SlimStack™ 0.35mm pitch Board-to-Board Connectors |
| Product Literature Order No    | 987651-8281                                       |
| Product Name                   | SlimStack                                         |
| Series Name                    | SSB6RP, SSB7RP                                    |
| UPC                            | 191128261753                                      |
| Physical                       |                                                   |
| Breakaway                      | No                                                |
| Circuits (Loaded)              | 34                                                |
| Circuits (maximum)             | 34                                                |
| Color - Resin                  | Black                                             |
| Durability (mating cycles max) | 30                                                |
| Glow-Wire Capable              | No                                                |
| Mated Height                   | 0.60mm, 0.70mm                                    |
| Mated Width                    | 2.00mm                                            |
| Material - Metal               | Copper Alloy                                      |
| Material - Plating Mating      | Gold over Nickel                                  |
| Material - Plating Termination | Gold over Nickel                                  |
| Material - Resin               | Liquid Crystal Polymer                            |
| Net Weight                     | 8.438/mg                                          |
| Number of Rows                 | 2                                                 |
| Orientation                    | Vertical                                          |
| PCB Retention                  | Yes                                               |
| Packaging Type                 | Embossed Tape on Reel                             |
| Pitch - Mating Interface       | 0.35mm                                            |
| Plating min - Mating           | 0.102µm                                           |
| Plating min - Termination      | 0.051µm                                           |
| Polarized to Mating Part       | No                                                |
| Polarized to PCB               | No                                                |
| Temperature Range - Operating  | -40° to +85°C                                     |
| Termination Interface: Style   | Surface Mount                                     |
| Electrical                     |                                                   |
| Current - Maximum per Contact  | 0.3A                                              |
| Voltage - Maximum              | 50V AC (RMS)/DC                                   |
| Material Info                  |                                                   |
| Reference - Drawing Numbers    |                                                   |
| Packaging Specification        | 5050709200-203                                    |
| Product Specification          | 5050660000-014, 5050660000-A06                    |
| Sales Drawing                  | 5050700000-007, 5050701000-019                    |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - ED/61/2018 (27 June 2018)                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

505070 Series

Mates With

SlimStack Armor Receptacle 505066 , 505270

This document was generated on 11/23/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**