



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Primary Product Material: **Silicone**

Primary Product Color: **Yellow**

Cavity Diameter: **8.5 mm [.334 in]**

Compatible Insulation Diameter Range: **2.1 mm [.083 in]**

Features

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

Body Features

Primary Product Material	Silicone
Primary Product Color	Yellow

Dimensions

Cavity Diameter	8.5 mm[.334 in]
Compatible Insulation Diameter Range	2.1 mm[.083 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Industry Standards

UL Flammability Rating	None
------------------------	------

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-H3399-CH8172
Heavy Duty Sealed Connector Series Housings



TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB




TE Part # 2301461-1
30POS, HYBRID, TAB HSG ASSY, SLD, COD A




TE Part # 2301462-1
30POS, HYBRID, REC HSG ASSY, SLD, COD A



TE Part # 1-2344950-1
95POS, HYBRID, REC HSG, ASSY,
COD A



TE Part # 2-1564536-1
4POS,TAB5.8X0.8,TABHSG,ASSY,
COD. B



TE Part # 2-2344950-1
95POS, HYBRID, REC HSG, ASSY,
COD B




TE Part # 2301461-2
30POS,HYBRID,TAB HSG ASSY,SLD,
COD B

Also in the Series | AMP MCP 6.3/4.8K



Automotive Housings(10)



Automotive Terminals(30)



Connector Seals & Cavity Plugs(1)



Other Automotive Connector
Accessories(1)

Customers Also Bought



TE Part #5-2297790-1
2POS,HPF 1.2,REC HSG,ASSY,SLD



TE Part #HD16-9-96SE
PLG, 9P, GRY, E, THRD, 16



TE Part #5053046037
RNF-100-3/16-0-25MM



TE Part #1456987-1
2x4 Fem unsealed LP assy Key A



TE Part #2112046-2
COVER,90,FOR 26POS



TE Part #2359941-6
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part #444156-4
.250 FASTON REC.



TE Part #8-1564284-5
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part #1355541-2
UMGEH M.SCHIEBER32P



TE Part #1355528-2
MPQ 2.KONT-SICHNG8P



Documents

Product Drawings

SINGLE WIRE SEAL,AMP MCP6.3/4.8K,YW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2177018-1_A_c-2177018-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2177018-1_A_c-2177018-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2177018-1_A_c-2177018-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS Catalog

English

CONNECTOR SELECTOR

English