

D-UKKB 3/5 BU - End cover



2771104

<https://www.phoenixcontact.com/us/products/2771104>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, depth: 62 mm, width: 2.5 mm, height: 67 mm, color: blue

Commercial data

Item number	2771104
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
Catalog page	Page 472 (C-1-2019)
GTIN	4017918068202
Weight per piece (including packing)	5.053 g
Weight per piece (excluding packing)	4.82 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	End cover
Data management status	
Article revision	01

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, no longer than 24 h, -60°C to +70°C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Thread type	()
-------------	----

Material specifications

Color	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	2.5 mm
Height	67 mm
Depth	62 mm

D-UKKB 3/5 BU - End cover



2771104

<https://www.phoenixcontact.com/us/products/2771104>

Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com