









NOTES

5. 梱包数量 : 1,000個/リール
NUMBER OF CONNECTORS: 1,000 PIECES/REEL
6. リードテープ長さ
LEAD TAPE LENGTH



7. トップテープの剥離強度はJIS C0806-3に準拠
TOP TAPE PEELING FORCE IS DEFINED BY JIS C0806-3.
8. 本製品は乾燥剤入り、ハイバリア梱包による納入である
THIS PRODUCT IS DELIVERED IN A HIGH-BARRIER PACKAGE WITH DESICCANT

49.4	45.4	20.2	40.4	44±0.3	15
					14
					13
					12
					11
					10
37.4	33.4	14.2	28.4	32±0.3	9
					8
					7
					6
29.4	25.4	11.5	-	24 ^{+0.3} _{-0.1}	5
					4
					3
					2
K	J	H	G	エンボステープ幅F WIDTH OF TAPE	極数 CKT. NO.


番号 No.	部品 PART	材質 MATERIAL
④	エンボステープ EMBOSSSED TAPE	ポリスチレン(PS) POLYSTYLENE
⑤	トップテープ TOP TAPE	ポリエチレン、ポリエチレンテレフタレート POLYETHYLENE (PE), POLYETHYLENE TELEPHTHALATE(PET)
⑥	リール REEL	ポリスチレン (リサイクル材を含む) POLYSTYLENE (CONTAINED RECYCLED MATERIAL)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex CLIK-MATE 1.5 SINGLE ROW SMT R/A TYPE REC ASSY GOLD PLATING					
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)				PRODUCT CUSTOMER DRAWING								
ANGULAR TOL		± 3.0 °										
4 PLACES		± 0.2										
3 PLACES		± 0.2										
2 PLACES		± 0.2										
INITIAL REVISION:				DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION			
1 PLACE		± 0.2		DRWN: MIKEDA01			2132260000-SD			PSD	000	E
0 PLACES		± 0.2		APPR: AIDA			2019/10/01			2019/11/20		
APPR: KOMURAKAMI												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
						A3-SIZE	213226			GENERAL		3 OF 5

△ 適用製品及び各種仕様書
APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKAGING SPECIFICATION	PART NUMBER	DOCUMENT NUMBER
	213226 ****	2132269200-SPK

適用嵌合相手 MATE WITH	HOUSING	TERMINAL (GOLD PLATING)		
		PLATING THK	#24-28	#28-30
製品番号 PRODUCT NUMBER	502578 ****	0.1 micro-meters	213028 1*00	213029 1*00
		0.38 micro-meters	213028 3*00	213029 3*00
		0.76 micro-meters	213028 7*00	213029 7*00
製品仕様書 PRODUCT SPECIFICATION	5025780004-PS			
アプリケーション仕様書 APPLICATION SPECIFICATION	AS-502578-00* (*: 1...JAPANESE, 2...ENGLISH)			



嵌合図
MATED CONNECTORS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex								
mm		NTS													
GENERAL TOLERANCES (UNLESS SPECIFIED)				CLIK-MATE 1.5 SINGLE ROW SMT R/A TYPE REC ASSY GOLD PLATING PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 2132260000-SD DOC TYPE PSD DOC PART 000 REVISION E											
ANGULAR TOL ± 3.0 °															
4 PLACES		± 0.2													
3 PLACES		± 0.2													
2 PLACES		± 0.2													
1 PLACE		± 0.2		EC NO: 742719 DRWN: MIKEDA012023/06/23 CHK'D: SAKIYAMA2023/06/23 APPR: AIDA2023/06/23 INITIAL REVISION: DRWN: MIKEDA012019/10/01 APPR: KOMURAKAMI2019/11/20											
0 PLACES		± 0.2													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		213226				GENERAL		4 OF 5	

10	9	8	7	6	5	4	3	2	1																																																																																
△4 製品一覧 PRODUCTS LIST																																																																																									
<table><tr><th>黒 BLACK</th><th>ナチュラル NATURAL</th><th colspan="2">HOUSING COLOR</th></tr><tr><td>213226 1511</td><td>213226 1510</td><td>15</td><td rowspan="14">213226 **1* (GOLD PLATING THICKNESS: 0.1 micro-meters MIN)</td></tr><tr><td>213226 1411</td><td>213226 1410</td><td>14</td></tr><tr><td>213226 1311</td><td>213226 1310</td><td>13</td></tr><tr><td>213226 1211</td><td>213226 1210</td><td>12</td></tr><tr><td>213226 1111</td><td>213226 1110</td><td>11</td></tr><tr><td>213226 1011</td><td>213226 1010</td><td>10</td></tr><tr><td>213226 0911</td><td>213226 0910</td><td>9</td></tr><tr><td>213226 0811</td><td>213226 0810</td><td>8</td></tr><tr><td>213226 0711</td><td>213226 0710</td><td>7</td></tr><tr><td>213226 0611</td><td>213226 0610</td><td>6</td></tr><tr><td>213226 0511</td><td>213226 0510</td><td>5</td></tr><tr><td>213226 0411</td><td>213226 0410</td><td>4</td></tr><tr><td>213226 0311</td><td>213226 0310</td><td>3</td></tr><tr><td>213226 0211</td><td>213226 0210</td><td>2</td></tr><tr><td colspan="2">オーダー番号 ORDER No</td><td>極数 CKT</td><td>MODEL NO</td></tr></table>										黒 BLACK	ナチュラル NATURAL	HOUSING COLOR		213226 1511	213226 1510	15	213226 **1* (GOLD PLATING THICKNESS: 0.1 micro-meters MIN)	213226 1411	213226 1410	14	213226 1311	213226 1310	13	213226 1211	213226 1210	12	213226 1111	213226 1110	11	213226 1011	213226 1010	10	213226 0911	213226 0910	9	213226 0811	213226 0810	8	213226 0711	213226 0710	7	213226 0611	213226 0610	6	213226 0511	213226 0510	5	213226 0411	213226 0410	4	213226 0311	213226 0310	3	213226 0211	213226 0210	2	オーダー番号 ORDER No		極数 CKT	MODEL NO																													
黒 BLACK	ナチュラル NATURAL	HOUSING COLOR																																																																																							
213226 1511	213226 1510	15	213226 **1* (GOLD PLATING THICKNESS: 0.1 micro-meters MIN)																																																																																						
213226 1411	213226 1410	14																																																																																							
213226 1311	213226 1310	13																																																																																							
213226 1211	213226 1210	12																																																																																							
213226 1111	213226 1110	11																																																																																							
213226 1011	213226 1010	10																																																																																							
213226 0911	213226 0910	9																																																																																							
213226 0811	213226 0810	8																																																																																							
213226 0711	213226 0710	7																																																																																							
213226 0611	213226 0610	6																																																																																							
213226 0511	213226 0510	5																																																																																							
213226 0411	213226 0410	4																																																																																							
213226 0311	213226 0310	3																																																																																							
213226 0211	213226 0210	2																																																																																							
オーダー番号 ORDER No		極数 CKT	MODEL NO																																																																																						
<table><tr><th>黒 BLACK</th><th>ナチュラル NATURAL</th><th colspan="2">HOUSING COLOR</th></tr><tr><td>213226 1531</td><td>213226 1530</td><td>15</td><td rowspan="14">213226 **3* (GOLD PLATING THICKNESS: 0.38 micro-meters MIN)</td></tr><tr><td>213226 1431</td><td>213226 1430</td><td>14</td></tr><tr><td>213226 1331</td><td>213226 1330</td><td>13</td></tr><tr><td>213226 1231</td><td>213226 1230</td><td>12</td></tr><tr><td>213226 1131</td><td>213226 1130</td><td>11</td></tr><tr><td>213226 1031</td><td>213226 1030</td><td>10</td></tr><tr><td>213226 0931</td><td>213226 0930</td><td>9</td></tr><tr><td>213226 0831</td><td>213226 0830</td><td>8</td></tr><tr><td>213226 0731</td><td>213226 0730</td><td>7</td></tr><tr><td>213226 0631</td><td>213226 0630</td><td>6</td></tr><tr><td>213226 0531</td><td>213226 0530</td><td>5</td></tr><tr><td>213226 0431</td><td>213226 0430</td><td>4</td></tr><tr><td>213226 0331</td><td>213226 0330</td><td>3</td></tr><tr><td>213226 0231</td><td>213226 0230</td><td>2</td></tr><tr><td colspan="2">オーダー番号 ORDER No</td><td>極数 CKT</td><td>MODEL NO</td></tr></table>										黒 BLACK	ナチュラル NATURAL	HOUSING COLOR		213226 1531	213226 1530	15	213226 **3* (GOLD PLATING THICKNESS: 0.38 micro-meters MIN)	213226 1431	213226 1430	14	213226 1331	213226 1330	13	213226 1231	213226 1230	12	213226 1131	213226 1130	11	213226 1031	213226 1030	10	213226 0931	213226 0930	9	213226 0831	213226 0830	8	213226 0731	213226 0730	7	213226 0631	213226 0630	6	213226 0531	213226 0530	5	213226 0431	213226 0430	4	213226 0331	213226 0330	3	213226 0231	213226 0230	2	オーダー番号 ORDER No		極数 CKT	MODEL NO																													
黒 BLACK	ナチュラル NATURAL	HOUSING COLOR																																																																																							
213226 1531	213226 1530	15	213226 **3* (GOLD PLATING THICKNESS: 0.38 micro-meters MIN)																																																																																						
213226 1431	213226 1430	14																																																																																							
213226 1331	213226 1330	13																																																																																							
213226 1231	213226 1230	12																																																																																							
213226 1131	213226 1130	11																																																																																							
213226 1031	213226 1030	10																																																																																							
213226 0931	213226 0930	9																																																																																							
213226 0831	213226 0830	8																																																																																							
213226 0731	213226 0730	7																																																																																							
213226 0631	213226 0630	6																																																																																							
213226 0531	213226 0530	5																																																																																							
213226 0431	213226 0430	4																																																																																							
213226 0331	213226 0330	3																																																																																							
213226 0231	213226 0230	2																																																																																							
オーダー番号 ORDER No		極数 CKT	MODEL NO																																																																																						
<table><tr><th>黒 BLACK</th><th>ナチュラル NATURAL</th><th colspan="2">HOUSING COLOR</th></tr><tr><td>213226 1571</td><td>213226 1570</td><td>15</td><td rowspan="14">213226 **7* (GOLD PLATING THICKNESS: 0.76 micro-meters MIN)</td></tr><tr><td>213226 1471</td><td>213226 1470</td><td>14</td></tr><tr><td>213226 1371</td><td>213226 1370</td><td>13</td></tr><tr><td>213226 1271</td><td>213226 1270</td><td>12</td></tr><tr><td>213226 1171</td><td>213226 1170</td><td>11</td></tr><tr><td>213226 1071</td><td>213226 1070</td><td>10</td></tr><tr><td>213226 0971</td><td>213226 0970</td><td>9</td></tr><tr><td>213226 0871</td><td>213226 0870</td><td>8</td></tr><tr><td>213226 0771</td><td>213226 0770</td><td>7</td></tr><tr><td>213226 0671</td><td>213226 0670</td><td>6</td></tr><tr><td>213226 0571</td><td>213226 0570</td><td>5</td></tr><tr><td>213226 0471</td><td>213226 0470</td><td>4</td></tr><tr><td>213226 0371</td><td>213226 0370</td><td>3</td></tr><tr><td>213226 0271</td><td>213226 0270</td><td>2</td></tr><tr><td colspan="2">オーダー番号 ORDER No</td><td>極数 CKT</td><td>MODEL NO</td></tr></table>										黒 BLACK	ナチュラル NATURAL	HOUSING COLOR		213226 1571	213226 1570	15	213226 **7* (GOLD PLATING THICKNESS: 0.76 micro-meters MIN)	213226 1471	213226 1470	14	213226 1371	213226 1370	13	213226 1271	213226 1270	12	213226 1171	213226 1170	11	213226 1071	213226 1070	10	213226 0971	213226 0970	9	213226 0871	213226 0870	8	213226 0771	213226 0770	7	213226 0671	213226 0670	6	213226 0571	213226 0570	5	213226 0471	213226 0470	4	213226 0371	213226 0370	3	213226 0271	213226 0270	2	オーダー番号 ORDER No		極数 CKT	MODEL NO																													
黒 BLACK	ナチュラル NATURAL	HOUSING COLOR																																																																																							
213226 1571	213226 1570	15	213226 **7* (GOLD PLATING THICKNESS: 0.76 micro-meters MIN)																																																																																						
213226 1471	213226 1470	14																																																																																							
213226 1371	213226 1370	13																																																																																							
213226 1271	213226 1270	12																																																																																							
213226 1171	213226 1170	11																																																																																							
213226 1071	213226 1070	10																																																																																							
213226 0971	213226 0970	9																																																																																							
213226 0871	213226 0870	8																																																																																							
213226 0771	213226 0770	7																																																																																							
213226 0671	213226 0670	6																																																																																							
213226 0571	213226 0570	5																																																																																							
213226 0471	213226 0470	4																																																																																							
213226 0371	213226 0370	3																																																																																							
213226 0271	213226 0270	2																																																																																							
オーダー番号 ORDER No		極数 CKT	MODEL NO																																																																																						
<table><tr><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="2">CURRENT REV DESC:</td><td colspan="4"> molex </td></tr><tr><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">EC NO: 742719</td><td colspan="4">CLIK-MATE 1.5</td></tr><tr><td colspan="2">ANGULAR TOL ± 3.0 °</td><td colspan="2">DRWN: MIKEDA01</td><td colspan="4">SINGLE ROW SMT R/A TYPE REC ASSY GOLD PLATING</td></tr><tr><td colspan="2">4 PLACES ± 0.2</td><td colspan="2">CHK'D: SAKIYAMA</td><td colspan="4">PRODUCT CUSTOMER DRAWING</td></tr><tr><td colspan="2">3 PLACES ± 0.2</td><td colspan="2">APPR: AIDA</td><td colspan="4">DOCUMENT NUMBER</td></tr><tr><td colspan="2">2 PLACES ± 0.2</td><td colspan="2">INITIAL REVISION:</td><td colspan="4">2132260000-SD</td></tr><tr><td colspan="2">1 PLACE ± 0.2</td><td colspan="2">DRWN: MIKEDA01</td><td colspan="2">PSD</td><td colspan="2">000</td></tr><tr><td colspan="2">0 PLACES ± 0.2</td><td colspan="2">APPR: KOMURAKAMI</td><td colspan="2">2019/10/01</td><td colspan="2">E</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIRD ANGLE PROJECTION</td><td colspan="2">SERIES</td><td colspan="2">SHEET NUMBER</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">A3-SIZE</td><td colspan="2">5 OF 5</td></tr></table>										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex				GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 742719		CLIK-MATE 1.5				ANGULAR TOL ± 3.0 °		DRWN: MIKEDA01		SINGLE ROW SMT R/A TYPE REC ASSY GOLD PLATING				4 PLACES ± 0.2		CHK'D: SAKIYAMA		PRODUCT CUSTOMER DRAWING				3 PLACES ± 0.2		APPR: AIDA		DOCUMENT NUMBER				2 PLACES ± 0.2		INITIAL REVISION:		2132260000-SD				1 PLACE ± 0.2		DRWN: MIKEDA01		PSD		000		0 PLACES ± 0.2		APPR: KOMURAKAMI		2019/10/01		E		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		SERIES		SHEET NUMBER						A3-SIZE		5 OF 5	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex																																																																																					
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 742719		CLIK-MATE 1.5																																																																																					
ANGULAR TOL ± 3.0 °		DRWN: MIKEDA01		SINGLE ROW SMT R/A TYPE REC ASSY GOLD PLATING																																																																																					
4 PLACES ± 0.2		CHK'D: SAKIYAMA		PRODUCT CUSTOMER DRAWING																																																																																					
3 PLACES ± 0.2		APPR: AIDA		DOCUMENT NUMBER																																																																																					
2 PLACES ± 0.2		INITIAL REVISION:		2132260000-SD																																																																																					
1 PLACE ± 0.2		DRWN: MIKEDA01		PSD		000																																																																																			
0 PLACES ± 0.2		APPR: KOMURAKAMI		2019/10/01		E																																																																																			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		SERIES		SHEET NUMBER																																																																																			
				A3-SIZE		5 OF 5																																																																																			
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2023/06/23</td><td>10:36:42</td></tr></table>										DOCUMENT STATUS	P1	RELEASE DATE	2023/06/23	10:36:42																																																																											
DOCUMENT STATUS	P1	RELEASE DATE	2023/06/23	10:36:42																																																																																					
10	9	8	7	6	5	4	3	2	1																																																																																