

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1600783023

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Hybrid Sealed Female Connector Assembly, Dual Row, 8 Circuits, Keying Option A, with Connector Position Assurance, Terminals 1, 2, 3, 4, 5, and 6 Plugged, Black



Documents:

Drawing (PDF)

Application Specification 1601110001-AS-000 (PDF)

Packaging Specification PK-31300-903-001 (PDF)

Test Summary TS-160076-2401G-001 (PDF)

Test Summary TS-160076-2401U-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	160078
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	With Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	
Product Name	MX150
UPC	191128224932
Physical	
Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	22.450/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Material Info	
Engineering Number	CVP-1600783023
Reference - Drawing Numbers	
Application Specification	1601110001-AS-000
Packaging Specification	PK-31300-903-001
Sales Drawing	999-S-010-2-Z01-001, SD-160076-0002-001
Test Summary	TS-160076-2401_G-001, TS-160076-2401_U-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

160078 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION