



Part Number : [191600041](#)
Product Description : Twist Lock Splice for 22-14 AWG Wire, Orange
Series Number : 19160
Status : Active
Product Category : Splices
Engineering Number : TL-O



Documents & Resources

Drawings


[Drawing 191600041_sd.pdf](#)

Specifications

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19160
Description	Twist Lock Splice for 22-14 AWG Wire, Orange
Product Family	Splices
Product Name	Closed-End Twist Lock
UPC	800753110458

Agency

CSA	LR700095
UL	E32244

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Orange
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.341/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	9.91mm max.

Wire Size (AWG)	14, 16, 18, 20, 22
-----------------	--------------------