

Product data sheet

Characteristics

9001SKS73B

Harmony 9001SK, selector switch head, plastic, standard handle, black, 30mm, 3 positions, spring return right to center



Main

| | |
|---------------------------|--|
| Bezel material | Plastic |
| Device short name | K |
| Enclosure type | Dust and oil resistant weatherproof enclosure indoor/outdoor |
| Mounting diameter | 1.18 in (30 mm) |
| Product or Component Type | Head for selector switch |
| Range of Product | Harmony 9001SK |

Complementary

| | |
|-------------------------------|-------------------------------|
| Cap/operator or lens colour | black |
| Contacts type and composition | Without contact block |
| Operator position information | 3 positions |
| Operator profile | Standard handle |
| Operator profile | 1 projecting push-button |
| Size | 30 mm |
| Type of operator | Spring return right to centre |

Environment

| | |
|---------------------------|---|
| NEMA Degree of Protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Product Certifications | CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR |

Ordering and shipping details

| | |
|-----------------------|--------------------|
| Category | 21429-9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 785901856641 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.08 oz (58.967 g) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 7.62 in (19.355 cm) |
| Package 1 width | 3.00 in (7.62 cm) |
| Package 1 Length | 19.35 in (49.161 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|