



Connectors > Lighting Connectors > Plug & Socket Lighting Connectors



Connector System: **Cable-to-Board**
Number of Positions: **2**
Sealable: **No**
Connector & Contact Terminates To: **Printed Circuit Board**
Lighting Connector Style: **Plug**

Features

Product Type Features

Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Lighting Connector Style	Plug
Connector Product Type	Connector Assembly

Configuration Features

Keying Arrangement	LV-2
Number of Positions	2

Electrical Characteristics

Operating Voltage	42 VDC
-------------------	--------

Body Features

Primary Product Color	White
Product Orientation	Straight



Contact Features

Contact Type	Socket
--------------	--------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts






TE Part # 293387-4
NECTOR S OUTLET LV-2 WHITE




TE Part # 293655-3
NECTOR S PCB PLUG STR HV-4 WHITE

Also in the Series


NECTOR S




Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug & Socket Lighting Connector Accessories(57)



Plug & Socket Lighting Connectors(54)

Customers Also Bought



TE Part #293651-4
CONTACT + HOUSING ASSY



TE Part #1586379-1
06P UMNL PLUG HSG NATL



TE Part #2266019-1
OCEAN_2.0_APPLICATOR-S-.080F-RSM



TE Part #2836287-1
OCEAN_2.0_Applicator-S-062F-RSM



TE Part #293653-5
NECTOR S PCB CONN. ASSY. STRAIGHT PLUG



TE Part #293654-5
NECTOR S-Line PCB assy 90deg. rec.



TE Part #3-1633621-1
ANVIL, COMBINATION



TE Part #4-1803257-3
ANVIL, COMBINATION END FEED



TE Part #63903-1
MAG-MATE SLIM LINE POSTED TPBR



TE Part #2213242-1
NECTOR M HSG, PIN, FH, 7P CODE A



Documents

Product Drawings

NECTOR S PCB PLUG STR LV-2 WHITE

English

CAD Files

Customer View Model

ENG_CVM_CVM_293655-5_B1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293655-5_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293655-5_B1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English