


General information

Part number	K41F1C-P03LPH0-400S	
Termination	solder	
Size	1	
Locking principle	break, push	
Coding	1_halfshell	
Cable Diameter	cable_mini_40	
Cable outlet	bend_relief	



Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	3	
Contact type	sockets	
Contact diameter	13mm	
Insulator material	peek	
Wire cross section	20_awg	
Termination	solder	
Termination diameter	11mm	

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	10_mm	08_mm
Nominal current single contact	12_a	iec_60512_5_2
Nominal current insert	12_A	vde_0298_4
Test voltage	15_kv_ac	sae_13441
safety_text		

Mechanical and environmental data

Degree of protection*	ip68
Operating temperature	40_120_c
Mating cycles	5000

mated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2

ul_text

illustrative_text