







THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED.				molex						
mm		NTS												
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 621109 DRWN: HCGOH 2019/07/23 CHK'D: NZENG 2019/09/02 APPR: SHONG 2019/09/03				MIRROR MEZZ, 2.5MM HEIGHT						
ANGULAR TOL ± °														
4 PLACES		±												
3 PLACES		±												
2 PLACES		± 0.2												
1 PLACE		±		INITIAL REVISION: DRWN: HCGOH 2019/05/15 APPR: SHONG 2019/07/02				PRODUCT CUSTOMER DRAWING						
0 PLACES		±						DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE		SERIES 209141		2091410001		PSD	000	A1
										MATERIAL NUMBER		CUSTOMER	SHEET NUMBER	
										SEE CHART		GENERAL MARKET		1 OF 4



10		9		8		7		6		5		4		3		2		1								
F						MATERIAL NO.	NO. OF ROW (ZONE I, II& III)	NO. OF DIFFERENTIAL PAIR PER ROW IN ZONE II (EXCLUDING ORPHAN PAIR)	NO. OF DIFFERENTIAL PAIR PER ROW IN ZONE I & III (EXCLUDING ORPHAN PAIR)	TOTAL NO. OF DIFFERENTIAL PAIR (EXCLUDING ORPHAN PAIR)	TOTAL NO. OF ORPHAN PAIR	TOTAL NO. OF S. BALL	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G	DIM H	DIM J	F				
						209141-0504	05	04	03	16	05	84	24.00	11.10	19.0	24.0	13.00	9.6	7.2	9.6	9.4					
						209141-0510		10	09	46		204	48.00		43.0	48.0			14.6	18.8	21.4					
						209141-0704	07	04	03	24	07	124	24.00	14.10	19.0	24.0	16.00	12.3	7.2	9.6	9.4					
						209141-0002		10	09	66		292	48.00		43.0	48.0			14.6	18.8	21.4					
						209141-1104	11	04	03	40	11	204	24.00	20.10	19.0	24.0	22.00	18.8	7.2	9.6	9.4					
						209141-1110		10	09	106		468	48.00		43.0	48.0			14.6	18.8	21.4					
						E			209141-1504	15	04	03	56	15	284	24.00	26.10	19.0	24.0	28.00	24.6			7.2	9.6	9.4
									209141-1510		10	09	146		644	48.00		43.0	48.0					14.6	18.8	21.4
									209141-2504	25	04	03	96	25	484	24.00	41.10	19.0	24.0	43.00	39.6			7.2	9.6	9.4
209141-2510	10	09	246	1084	48.00				43.0		48.0	14.6	18.8		21.4											
D																										



209141-0504 PIN MAPPING (MAIN BOARD- MATING BOARD)								
/	/	A3-E3	A4-E4	...	A17-E17	A18-E18	/	/
/	/	B3-D3	B4-D4	...	B17-D17	B18-D18	/	/
C1-C1	C2-C2	C3-C3	C4-C4	...	C17-C17	C18-C18	C19-C19	C20-C20
/	/	D3-B3	D4-B4	...	D17-B17	D18-B18	/	/
/	/	E3-A3	E4-A4	...	E17-A17	E18-A18	/	/



209141-1110 PIN MAPPING (MAIN BOARD-MATING BOARD)								
/	/	A3-L3	A4-L4	...	A41-L41	A42-L42	/	/
/	/	B3-K3	B4-K4	...	B41-K41	B42-K42	/	/
C1-J1	C2-J2	C3-J3	C4-J4	...	C41-J41	C42-J42	C43-J43	C44-J44
D1-H1	D2-H2	D3-H3	D4-H4	...	D41-H41	D42-H42	D43-H43	D44-H44
E1-G1	E2-G2	E3-G3	E4-G4	...	E41-G41	E42-G42	E43-G43	E44-G44
F1-F1	F2-F2	F3-F3	F4-F4	...	F41-F41	F42-F42	F43-F43	F44-F44
G1-E1	G2-E2	G3-E3	G4-E4	...	G41-E41	G42-E42	G43-E43	G44-E44
H1-D1	H2-D2	H3-D3	H4-D4	...	H41-D41	H42-D42	H43-D43	H44-D44
J1-C1	J2-C2	J3-C3	J4-C4	...	J41-C41	J42-C42	J43-C43	J44-C44
/	/	K3-B3	K4-B4	...	K41-B41	K42-B42	/	/
/	/	L3-A3	L4-A4	...	L41-A41	L42-A42	/	/

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS mm		SCALE NTS		CURRENT REV DESC: REVISED.				molex	
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		± °		EC NO: 621109 DRWN: HCGOH 2019/07/23 CHK'D: NZENG 2019/09/02 APPR: SHONG 2019/09/03				MIRROR MEZZ, 2.5MM HEIGHT	
4 PLACES		±							
3 PLACES		±		INITIAL REVISION: DRWN: HCGOH 2019/05/15 APPR: SHONG 2019/07/02				PRODUCT CUSTOMER DRAWING	
2 PLACES		± 0.2							
1 PLACE		±		DOCUMENT NUMBER 2091410001				DOC TYPE PSD	
0 PLACES		±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING A3-SIZE		SERIES 209141		SHEET NUMBER 4 OF 4	