

FC to SC 50/125 OM3 10 Gb Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-SC10G**



Highlights

- Converts native FC jack to an SC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 50/125 OM3 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

Package Includes

- T020-001-SC10G FC to SC 50/125 OM3 10 Gb Adapter

Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an SC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

Description

The T020-001-SC10G FC to SC 10 Gb Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an SC female port for 50/125 OM3 multimode cable testing. "OM3" is clearly labeled on the unit to differentiate the T020-001-SC10G from other adapters. Included dust caps keep the connectors clean when not in use.

Features

Converts Cable Tester's FC Connector to an SC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 50/125 OM3 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

Specifications

OVERVIEW	
UPC Code	037332197627
Technology	Multimode
Optical Mode	OM3
PHYSICAL	
Color	Silver
Clad Diameter (microns)	125



Powering Business Worldwide

TRIPP LITE
SERIES

Core Diameter (microns)	50
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.