




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
PCB Mount Retention	Without
Mating Retention	Without



Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Entry Configuration	Both Ends Closed
Housing Material	PBT GV15
Centerline (Pitch)	2.54 mm[.1 in]
Dimensions	
Row-to-Row Spacing	2.54 mm[.1 in]
Usage Conditions	
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	1000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5-87165-2 LOCKING CLIP ASSY .025 SQ LP	 TE Part # 87190-1 LOCKING CLIP CONT ASSY .025 SQ	 TE Part # 867052-2 LOCKING CLIP CONT ASSY .025 SQ	 TE Part # 5-87124-2 LOCKING CLIP CONT ASY .025 SQ
 TE Part # 87124-1 LOCKING CLIP CONT ASSY .025 SQ	 TE Part # 5-867052-1 LOCKING CLIP CONT ASSY .025 SQ	 TE Part # 5-87191-2 LOCKING CLIP ASSY .025 SQ LP	 TE Part # 87165-1 LOCKING CLIP ASSY .025 SQ LP
 TE Part # 87165-2 LOCKING CLIP ASSY .025 SQ LP	 TE Part # 867052-1 LOCKING CLIP CONT ASSY .025 SQ	 TE Part # 87191-1 LOCKING CLIP ASSY .025 SQ LP	 TE Part # 926329-1 KEYING PLUG

Also in the Series | AMPMODU LOCKING CLIP

 Connector Contacts(7)	 Connector Hardware(1)	 Insertion & Extraction Tools(2)	 Wire-to-Board Connector Assemblies & Housings(83)
--	---	--	--

Customers Also Bought







TE Part #166292-1
20DF COSI SOCKET



TE Part #2205066-1
CA MICRO-MATCH MOW-MOW
16POS




TE Part #5-87124-2
LOCKING CLIP CONT ASY .025 SQ




TE Part #87165-1
LOCKING CLIP ASSY .025 SQ LP



TE Part #1534807-1
HD20 COVER KIT 15P



TE Part #926657-7
7P LOCKG CLIP GEH



TE Part #926657-8
LOCKING CLIP HSG



TE Part #4-1618414-4
LEV200AKNAA=RELAY, SPST-NO



TE Part #K1161166
Micro Switch MZX1 361 304 901

Documents

Product Drawings

LOCKING CLIP HSG

English

CAD Files

Customer View Model

ENG_CVM_926657-4_E1.3d_igs.zip

English

Customer View Model

ENG_CVM_926657-4_E1.3d_stp.zip

English

Customer View Model

ENG_CVM_926657-4_E1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals



UL Report

English