

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2125153102

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Max Female Crimp Terminal, Tin over Nickel Plating, 16 AWG, Reel

Documents:

Drawing (PDF)

Product Specification 2125150000-PS-000 (PDF)

Packaging Specification 2125150001-PK-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

212515

Power, Wire-to-Board, Wire-to-Wire

Yes

Mini-Fit Family Power Connectors

Mini-Fit Max

193264598410

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

30

Female

High Conductivity Copper

Tin

Tin

0.310/g

Reel

Crimp or Compression

2.42mm Max.

16

N/A

Electrical

Voltage - Maximum

600V

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

2125150001-PK-000

2125150000-PS-000

2125150001-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

212515 Series

Use With

Mini-Fit Max Crimp Housing 212514

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for Mini-Fit MAX Receptacle Crimp Terminals, 16 AWG, UL1007 Wire	2133092300
Extraction and Activation Tool	638132700

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION