



Part Number : [1200680228](#)

Product Description : Micro-Change (M12) In-Line Splitter, 4 Poles, Female/Female with Male Drop

Series Number : 120068

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Number : 81589R



---

## Documents & Resources

### Drawings

[Drawing 1200680228\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Micro-Change (M12) In-Line Splitter, 4 Poles, Female/Female with Male Drop
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678841954

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	24V DC

### Physical

Color - Cable Jacket	Yellow
Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A

Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Net Weight	241.000/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +105°C

---

This document was generated on Sep 23, 2024