

Coaxial PCB Connector 82_BNC-50-0-1/133_N

Description

Straight PCB jack

Interface Standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0053 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013009
Catalogue drawing	DCA-00013001
Mounting hole	DOU-00012084

Ordering Information

Single package	82_BNC-50-0-1/133_NE
Tray package	82_BNC-50-0-1/133_NH

Remarks

PCB connector with stand-offs