

1886333
<https://www.phoenixcontact.com/us/products/1886333>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector component, degree of protection: IP20, Bus, connection method: Coupling

Commercial data

Item number	1886333
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCBZ
GTIN	4017918876678
Weight per piece (including packing)	11.49 g
Weight per piece (excluding packing)	11.49 g
Customs tariff number	85369010
Country of origin	DE

VC-DSUB 9-GC-BU/BU-SET - Connector component



1886333

<https://www.phoenixcontact.com/us/products/1886333>

Technical data

Product properties

Product type	Female insert
Type	D-SUB
Connection profile	D-SUB

Data management status

Article revision	02
------------------	----

Electrical properties

Transmission medium	Copper
---------------------	--------

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Dimensions

Width	18.2 mm
Height	31 mm
Length	12.6 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Thread type	()
-------------	----

VC-DSUB 9-GC-BU/BU-SET - Connector component



1886333

<https://www.phoenixcontact.com/us/products/1886333>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%