

FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 26-pos.

Commercial data

Item number	2281050
Packing unit	5 pc
Minimum order quantity	5 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	CK2181
Catalog page	Page 242 (IF-2007)
GTIN	4017918054502
Weight per piece (including packing)	147.64 g
Weight per piece (excluding packing)	130.854 g
Customs tariff number	85369010
Country of origin	DE

FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	26

Insulation characteristics

Insulation	Functional insulation
------------	-----------------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	$\leq 30 \text{ V AC}$
Operating voltage (DC)	$\leq 60 \text{ V DC}$
Current (per branch)	$\leq 1 \text{ A}$

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of positions	26
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve)
	0.25 mm ² ... 2.5 mm ² (Ferrule with plastic sleeve)
	0.2 mm ² ... 1.5 mm ²

FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

Conductor cross section flexible (2 conductors with same cross section)	0.25 mm² ... 0.75 mm² (Ferrule without plastic sleeve)
	0.5 mm² ... 0.5 mm² (TWIN ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

Signaling

Status display present	No
------------------------	----

Dimensions

Item dimensions

Width	78.75 mm
Height	77 mm
Depth	57.47 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide 6 green

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also
--------------------	--

FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>



be met.

FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>



Drawings

Circuit diagram



FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2281050>

cUL Recognized Approval ID: FILE E 118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Field wiring	125 V	1 A	30 - 12	-

UL Recognized Approval ID: FILE E 118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Field wiring	125 V	1 A	30 - 12	-

cULus Recognized				
------------------	--	--	--	--

FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>



Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 8.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

FLKM 26 - Interface module

2281050

<https://www.phoenixcontact.com/us/products/2281050>




Accessories

FLK EZ-DR.../.../... - Cable

2295059

<https://www.phoenixcontact.com/us/products/2295059>

Round cable, with preassembly, not shielded, variable cable length



FLK 26/EZ-DR/ 50/KONFEK - Cable

2299385

<https://www.phoenixcontact.com/us/products/2299385>

Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 0.5 m



FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

FLK 26/EZ-DR/ 100/KONFEK - Cable

2299398

<https://www.phoenixcontact.com/us/products/2299398>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 1 m

FLK 26/EZ-DR/ 150/KONFEK - Cable

2299408

<https://www.phoenixcontact.com/us/products/2299408>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 1.5 m

FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

FLK 26/EZ-DR/ 200/KONFEK - Cable

2299411

<https://www.phoenixcontact.com/us/products/2299411>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 2 m

FLK 26/EZ-DR/ 300/KONFEK - Cable

2299424

<https://www.phoenixcontact.com/us/products/2299424>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 3 m

FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

FLK 26/EZ-DR/ 400/KONFEK - Cable

2299437

<https://www.phoenixcontact.com/us/products/2299437>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 4 m

FLK 26/EZ-DR/ 600/KONFEK - Cable

2299440

<https://www.phoenixcontact.com/us/products/2299440>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 6 m

FLKM 26 - Interface module



2281050

<https://www.phoenixcontact.com/us/products/2281050>

FLK 26/EZ-DR/ 800/KONFEK - Cable

2299453

<https://www.phoenixcontact.com/us/products/2299453>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 8 m

FLK 26/EZ-DR/1000/KONFEK - Cable

2299466

<https://www.phoenixcontact.com/us/products/2299466>



Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 10 m

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com