

PROT-M12 FS-PA-CHAIN-EYE-DM12 - Sealing cap

1456187

<https://www.phoenixcontact.com/us/products/1456187>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M12 sealing cap made of plastic with fixing band, for free M12 plugs with 12.0 mm fastening eye



Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1456187 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AB27 |
| Product key | ABQZAB |
| Catalog page | Page 55 (C-2-2019) |
| GTIN | 4046356605700 |
| Weight per piece (including packing) | 4.65 g |
| Weight per piece (excluding packing) | 3.8 g |
| Customs tariff number | 39235090 |
| Country of origin | DE |

PROT-M12 FS-PA-CHAIN-EYE-DM12 - Sealing cap

1456187

<https://www.phoenixcontact.com/us/products/1456187>



Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Protective cap |
| Thread type | M12 |

Material specifications

| | |
|--|-----------|
| Material | PA 6.6 GF |
| | PUR |
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -25 °C ... 85 °C |

PROT-M12 FS-PA-CHAIN-EYE-DM12 - Sealing cap

1456187

<https://www.phoenixcontact.com/us/products/1456187>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440208 |
| ECLASS-12.0 | 27440208 |
| ECLASS-13.0 | 27440208 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002314 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PROT-M12 FS-PA-CHAIN-EYE-DM12 - Sealing cap

1456187

<https://www.phoenixcontact.com/us/products/1456187>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com