

Part Number : 389690003

Series Number : 38969

Product Category : Terminal Blocks and  
Barrier Strip

Product Description : 12.70mm Pitch, Single  
Row Tri-Barrier Terminal Strip, without  
Mounting Ends, 3 Circuits

Status : Active

## Documents & Resources

### Drawings

Drawing 389690003\_sd.pdf

### 3D Models and Design Files

3D Model 389690003\_stp.zip

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	38969
Description	12.70mm Pitch, Single Row Tri-Barrier Terminal Strip, without Mounting Ends, 3 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Fixed Mount Barrier
Type	Barrier and Terminal Strips
UPC	822350944946

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Entry Angle	Horizontal
Lock to Mating Part	None
Net Weight	25.600/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	4.00mm
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	12.70mm

Pitch - Termination Interface	12.70mm
Polarized to Mating Part	Yes
Shrouded	Tri-Barrier
Stackable	No
Temperature Range - Operating	-40° to +120°C
Wire Size (AWG)	10, 12, 14, 16, 18, 20, 8

---

---

This document was generated on May 24, 2024