



Part Number : 1300680099

Series Number : 130068

Product Category : Industrial Tees and Splitters

Product Description : BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Black

Status : Active

Engineering Number : TC40C40-200G

Documents & Resources

Drawings
Drawing 1300680099_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130068
Description	BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Black
IP Rating	IP67
Product Family	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Type	Power Tap Tee
UPC	78172536310

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	BradPower D-Size (1 3/8"-M35)
Drop Gender	Female
Keyway	Single
Left Trunk Connector	BradPower D-Size (1 3/8"-M35)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	458.000/g
Poles	4
Right Trunk Connector	BradPower D-Size (1 3/8"-M35)

Right Trunk Gender	Male
Temperature Range - Operating	-20°C to +90°C