

**Johanson Company: Johanson Technology inc.** Product Release Date: 28 October, 2008

Deprecated P/N: 0915AT43A0026E

Datasheet Date: 05-25-2024

Description: Antennas, 2708, 902-928MHz, 2W,  
-1dBi (typ), ISM Antenna for small form factor  
applications, Ni/Sn (RoHS), 7" Reel Embossed  
Tape

Life Cycle Stage: Active - Production

Schedule B: 8529

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Antennas

Product Subfamily: Antennas

Marking: Orientation Mark

Web Page Link:

<https://www.johansontechnology.com/antennas>

Thickness (Max): 0.035

Thickness (Min): 0.023

End Band (Min):

End Band (Max):

Standard Item: 1

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important  
to obtain a quotation with lead time for  
production planning purposes. 20

Length (Min): 0.268

Length (Max): 0.284

Width (Min): 0.071

Width (Max): 0.087

Packaging: 7" Reel Embossed Tape

Packaging Qty: 1000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -55°C to  
+125°CStorage Temp Range (Non Operating): +5°C to  
+40°C with RH 20% to 70%