

Safe-IT Blank Wall Plate, Antibacterial, Ivory Matte, TAA

MODEL NUMBER: N042AB-000-IVM



Clean, simple faceplate mounts to a wall to keep unused in-wall ports covered and protected.

Features

High-Impact Wall Plate Designed to Blend In Seamlessly with Your Room

This blank wall plate provides temporary or permanent cover for any unused in-wall gang ports or outlets. It protects the ports against debris, damage, tampering or unauthorized connections. This durable faceplate with an ivory matte finish blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Provides Extra Protection Against Certain Bacteria

The wall plate is constructed using an antibacterial material that is effective in inhibiting *Escherichia coli* (*E. coli*) and *Staphylococcus aureus* (staph) and tested to ISO 22196:2011 standards. This added protection makes this cover plate an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

TAA-Compliant for GSA Schedule Purchases

The N042AB-000-IVM is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Conceals unused wall ports to prevent damage, tampering or unauthorized connections
- Made with antibacterial material proven effective in inhibiting *E. coli* and staph
- High-impact plastic construction designed to blend in with your home/office décor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- N042AB-000-IVM Blank Antibacterial Wall Plate, Ivory Matte
- (2) Mounting screws

Specifications

OVERVIEW	
UPC Code	037332269089
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Global
PHYSICAL	
Color	Ivory



Powering Business Worldwide



Material of Construction	ABS (ABS-764)
Total Number of Ports	0
Unit Dimensions (hwd / in.)	4.840 x 3.110 x 0.240
Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 94; UL Listed; cUL Listed
Product Compliance	REACH; RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.