

注: 未经许可禁止传播、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

- 1.Rating voltage/current: 300V/10A
- 2.withstanding voltage: AC1500V/1Min
- 3.Torque value: M2.5, 3.54Lb.in
- 4.Wire range: 26~14AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	250V	/
Rate Current(A)	/	10A	/

2. Torque value: M2.5, 0.4Nm
- 3.wire range: 0.5~2.5mm²

NOTES2:

- 1.Housing: PA66(UL94V-0)
- 2.Solder Pin: Copper alloy(Sn Plated)
- 3.Spring: Stainless Steel
- 4.Screw: Steel(M2.5,Zn Plated)

NOTES3:

- 1.Pitch: 5.0mm Poles: 02-24P
- 2.Stripping length: 6-7mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order




MX126R	-	5.0	-	XXP	-	XXXX	-	XX	-	X	-	X
产品型号		间距		极数		颜色:						A-Z其他定制
						灰色:GY	橙色:OE	01:常规颜色				0:Y一字螺丝
						蓝色:BU	红色:RD	定制颜色				1:S十字螺丝
						黑色:BK	透明色:TT					2:PS平头十字螺丝
						绿色:GN	黄色:YW					Cu:铜方块
						白色:WE						Fe:铁方块

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CKK	DATE	22.09.14	UNITS	MM
CHK.		DATE		SCALE	1:1
APP.		DATE			
				NAME	MX126R-5.0-XXP
				DWGNO.	



CIXI MAIXU ELECTRONICS CO.,LTD.

慈溪市迈旭电子有限公司



PCB Layout

Pitch Range In mm	Nominal Dimension Range In mm	—	∩	□
TO 6	Over 6 TO 10	Over 10 TO 24	Over 24 TO 30	Over 30 TO 60
±0.15	±0.20	±0.30	±0.30	±0.50
				±0.70
				±1.00
				±1.30
				±2°