



## Summary

[Request a quote](#)

Number of contacts Low Voltage	2
Wire Size/AWG	30 - 26
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.10 - 3.50 mm
Size	0T
Series	T - Small Outdoor keyed

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	0T.511 - SPE - 2 High Speed, Low Voltage (1000BASE-T1 (IEEE 802.3bp))
Insulator	L: PEEK (UL 94 / V-0/1.5)
Number of contacts Low Voltage	2
Differentiated pairs (High speed)	1
Protocol	1000 Base-T1 (1Gb/s)
Wire Size/AWG	30 - 26
Gender	Standard

## Form & Material

Shell style / Model id	PH - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	21.62 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	>3000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [ 6 ms]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

---

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	3.10 - 3.50 mm

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/phg-0t-511-cllc35.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.