

# D-MBK 6/E - End cover



1413049

<https://www.phoenixcontact.com/us/products/1413049>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, width: 1.5 mm, height: 30.1 mm, color: gray

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1413049             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales key                            | BE19                |
| Product key                          | BE1Z1X              |
| Catalog page                         | Page 558 (C-1-2019) |
| GTIN                                 | 4017918021122       |
| Weight per piece (including packing) | 1.783 g             |
| Weight per piece (excluding packing) | 1.723 g             |
| Customs tariff number                | 85389099            |
| Country of origin                    | DE                  |

# D-MBK 6/E - End cover

1413049

<https://www.phoenixcontact.com/us/products/1413049>



## Technical data

### Product properties

|              |           |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Material specifications

|                                        |      |
|----------------------------------------|------|
| Color                                  | gray |
| Material                               | PA   |
| Flammability rating according to UL 94 | V2   |

### Dimensions

|        |         |
|--------|---------|
| Width  | 1.5 mm  |
| Height | 30.1 mm |

# D-MBK 6/E - End cover

1413049

<https://www.phoenixcontact.com/us/products/1413049>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27141133 |
| ECLASS-12.0 | 27141133 |
| ECLASS-13.0 | 27250301 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# D-MBK 6/E - End cover



1413049  
<https://www.phoenixcontact.com/us/products/1413049>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)