




注：本资料禁止传输、复制、编辑、存档，以及用其内容进行交流



NOTES1:
UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2. Torque value: M2.0, 1.77Lb.in
3. Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	II	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

2. Torque value: M2, 0.2Nm
3 wire range: 0.2~1.5mm²

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Cover: PA66 (UL94V-0)

3.Cage: Brass (Ni Plated)

4.Clamp: Copper alloy (Ni Plated)

5.Screw 1: Steel (M2.0,Zn Plated)

6.Screw 2: Steel (M2.5,Zn Plated)

NOTES3:

1.Pitch: 3.5mm Poles: 02~24P

2.Stripping length: 6~7mm

3.Operating temperature: -40℃~+105℃

4.RoHS Compliance

How to order

MX15EDGKM - 35 - XXP - XXXX - XX - X - X

产品型号

间距

颜色:

数量

01:常规颜色

灰色:GY 橙色:OE 02~99:

蓝色:BU 红色:RD 定制颜色

黑色:BK 透明色:TT

绿色:GN 黄色:YW

白色:WE

A-7其他定制

0:Y一字螺丝

1:S十字螺丝

2:P.S平头十字螺丝

Cu铜方块

Fe铁方块

Pitch Range In mm	Nominal Dimension Range In mm	—	—
-------------------	-------------------------------	---	---

Over 6 TO 6	Over 10 TO 24	Over 30 TO 30	Over 60 TO 60	Over 100 TO 100	Over 150 TO 150	0.1/10	±2°
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00		

REV	EC.N NO.	CONTENT	CHK	DATE
-----	----------	---------	-----	------

ITEM	NAME OF PART	NO. OF PART	Q.TY	MATERIAL	NOTE
DWG.	CKK	DATE	22.09.14	UNITS	MM
CHK.		DATE		SCALE	SHEET/OF 1/1
APP.		DATE			1:1 A4
					
					MX15EDGKM-3.5-XXP



CIXI MAIXU ELECTRONICS CO.,LTD.

慈溪市迈旭电子有限公司

DWGNO.