



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 7 Watt, 0.10-500 Ohm



Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **3 W**

Resistance Value: **1.5 Ω**

Resistance Class: **Up to 1k Ω**

[All SMD Power Resistor: 7 Watt, 0.10-500 Ohm \(229\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Power Rating	3 W
Resistance Value	1.5 Ω
Resistance Class	Up to 1k Ω
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	5 mm[.197 in]
Product Length	10.5 mm[.413 in]



Product Width	5.5 mm[.217 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	± 200 ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMW31R5JT

Power Resistor, Wire Wound, 3 W, 1.5 Ω , 5 %, ± 200 ppm/ $^{\circ}\text{C}$, Solder, 2 Termination, Height .197 in [5 mm], Length .413 in [10.5 mm], CGS SM



TE Part # CAT-C339-SM1
SMD Power Resistor: 7 Watt, 200-2M Ohm

TE Part # 1879233-9
SMW5 R22 5%

TE Part # 2-2176617-9
SMQW3W 1R5 5%

TE Part # 9-1879021-2
SMW3 R15 1%

Also in the Series | CGS SM

Battery Holders(1)

Expanded Beam Fiber Optics(9)

LC Connectors(2)

RJ14 Connectors(1)

RJ22 Connectors(1)

RJ25 Connectors(1)

RJ45 Connectors(3)

SC Connectors(2)

Surface Mount Resistors(554)

Customers Also Bought

TE Part # 1-338068-4
MICRO-MATCH FTE,14P

TE Part # 1-178294-5
DYNAMIC D3100 HDR ASY 4P H K/X

TE Part # 2-1879021-5
SMW3 1R0 5%

TE Part # 1761681-3
IDC LOW PRO HDR 10P VERT HT BLACK

SMW31R5JT

Power Resistor, Wire Wound, 3 W, 1.5 Ω , 5 %, ± 200 ppm/ $^{\circ}\text{C}$, Solder, 2 Termination,
Height .197 in [5 mm], Length .413 in [10.5 mm], CGS SM



TE Part # 0641-3-1231L
CONT PIN

TE Part # 2213763-3
AV19 SPL 3A NO LED

TE Part # 7-1879494-3
CRGH0603 5% 1K0 0.2W

TE Part # 323914
TERMINAL,PIDG R 26-22 4

TE Part # 1-1393788-1
V23079A1003B301

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1879021-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1879021-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1879021-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English