



Part Number : 1731120134

Series Number : 173112

Product Category : D-Sub Contacts

Product Description : FCT Pneumatic Contact, Male, Straight, Silver Plating, 2.00mm Tube Inner Diameter, with Plastic Retention Clip and Knurl

Status : Active

Engineering Number : FMG002P149KR

Documents & Resources

Specifications

Packaging Specification 1731120009-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT Pneumatic Contact, Male, Straight, Silver Plating, 2.00mm Tube Inner Diameter, with Plastic Retention Clip and Knurl
Contact Type	Pneumatic
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Mixed Layout
UPC	889056488891

Electrical

Current - Maximum per Contact	N/A
-------------------------------	-----

Physical

Durability (mating cycles max)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Material - Retaining Clip	PEI
Net Weight	1.300/g
Orientation	Straight
Packaging Type	Bag
Temperature Range - Operating	-10° to +60°C

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>