

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)

32_MMBX-50-0-6/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection

**Product configuration**

Interface type	Gender	Standard
MMBX	plug (male)	HUBER+SUHNER-MMBX
MMBX	plug (male)	HUBER+SUHNER-MMBX

Interface and material data

MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	12.4 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	26 dB	1.106
2.5 GHz ... 6 GHz	21 dB	1.196
6 GHz ... 12.4 GHz	12 dB	1.671

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)
32_MMBX-50-0-6/111_N

Mechanical data	
Weight	0.0007 kg
Mating cycles	100

Environmental data	
Operation temperature	-55 °C ... 155 °C

Ordering Information Table		
Item number	Item description	Packaging type
23022532	32_MMBX-50-0-6/111_NE	Single
84024341	32_MMBX-50-0-6/111_NH	Bulk 100 pcs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2314 / Date of publication: 12.04.2024 / uncontrolled copy