

AB-UTI/3 - Support bracket




3076038

<https://www.phoenixcontact.com/us/products/3076038>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Support bracket, Bracket for busbars, set every 20 cm, pitch: 200 mm, depth: 51.2 mm, width: 2.2 mm, height: 93.5 mm, number of positions: 1, color: blue



Your advantages

- Support bracket, to hold the neutral busbar

Commercial data

Item number	3076038
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2Z1X
Catalog page	Page 90 (C-3-2013)
GTIN	4046356644044
Weight per piece (including packing)	4.799 g
Weight per piece (excluding packing)	4.747 g
Customs tariff number	39269097
Country of origin	DE

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



Technical data

Product properties

Product type	Support bracket
Number of positions	1
Pitch	200 mm

Dimensions

Width	2.2 mm
End cover width	2.2 mm
Height	93.5 mm
Depth	51.2 mm
Depth on NS 35/7,5	51.5 mm
Depth on NS 35/15	59 mm
Pitch	200 mm

Material specifications

Color	blue
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

AB-UTI/3 - Support bracket



3076038

<https://www.phoenixcontact.com/us/products/3076038>

Classifications

ECLASS

ECLASS-11.0	27400607
ECLASS-12.0	27400607
ECLASS-13.0	27400607

ETIM

ETIM 9.0	EC001166
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



Accessories

NLS-CU 3/10 1600MM - Neutral conductor rail

5406430

<https://www.phoenixcontact.com/us/products/5406430>



NLS-CU 3/10 1160MM - Neutral conductor rail

5406429

<https://www.phoenixcontact.com/us/products/5406429>



AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 148MM 2X5,5 - Neutral conductor rail

5406390

<https://www.phoenixcontact.com/us/products/5406390>



NLS-CU 3/10 SN 55MM 2X5,5 - Neutral busbar

5406304

<https://www.phoenixcontact.com/us/products/5406304>



Neutral busbar, material: Copper, tin-plated

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 SN 300MM 2X5,2 - Neutral busbar

5406221

<https://www.phoenixcontact.com/us/products/5406221>



Neutral busbar

NLS-CU 3/10 SN 175MM - Neutral busbar

5406194

<https://www.phoenixcontact.com/us/products/5406194>



Neutral busbar

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 SN 630MM - Neutral busbar

5406185

<https://www.phoenixcontact.com/us/products/5406185>



Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 SN 550MM - Neutral busbar

5406184

<https://www.phoenixcontact.com/us/products/5406184>



Neutral busbar, material: Copper, tin-plated

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 SN 1550MM - Neutral busbar

5406170

<https://www.phoenixcontact.com/us/products/5406170>



Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 SN 93MM - Neutral busbar

5406159

<https://www.phoenixcontact.com/us/products/5406159>



Neutral busbar, material: Copper, tin-plated

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 16.31.19.040-AA - Neutral busbar

5405865

<https://www.phoenixcontact.com/us/products/5405865>



Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 95MM ZG.160452 - Neutral busbar

5405857

<https://www.phoenixcontact.com/us/products/5405857>



Neutral busbar, material: Copper, tin-plated

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 58MM ZG.155646 - Neutral busbar

5405855

<https://www.phoenixcontact.com/us/products/5405855>



Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 SN 90MM LANG - Neutral busbar

5405836

<https://www.phoenixcontact.com/us/products/5405836>



Neutral busbar, material: Copper, tin-plated

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 245MM LG - Neutral busbar

5405831

<https://www.phoenixcontact.com/us/products/5405831>



Neutral busbar, material: Copper, tin-plated

NLS 3/10 AV 134/134 - Neutral busbar

3062870

<https://www.phoenixcontact.com/us/products/3062870>



Angled rail for holding the C-NBB busbar connector

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 SN 150MM 2X3,5 - Neutral busbar

1044718

<https://www.phoenixcontact.com/us/products/1044718>



PEN conductor busbar, 3 mm x 10 mm

NLS-CU 3/10 220MM 4X4,5 1XM4 - Neutral busbar

1013677

<https://www.phoenixcontact.com/us/products/1013677>



PEN conductor busbar, 3 mm x 10 mm

AB-UTI/3 - Support bracket

3076038

<https://www.phoenixcontact.com/us/products/3076038>



NLS-CU 3/10 SN 1000MM - Neutral busbar

0402174

<https://www.phoenixcontact.com/us/products/0402174>



Neutral busbar, DIN VDE 0611-4: 1991-02, color: silver

NLS-CU 3/10 SN 2000MM - Neutral busbar

0402006

<https://www.phoenixcontact.com/us/products/0402006>



Neutral busbar, DIN VDE 0611-4: 1991-02, material: Copper, tin-plated, color: silver

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com