



Part Number : 1060597100

Series Number : 106059

Product Category : Fiber Optic Connectors

Product Description : Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Multimode Male with Logo


Status : Active

Documents & Resources

Drawings
Drawing 1060597100_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead monoxide; Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Connectors
Series	106059
Description	Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Multimode Male with Logo
Mode	Multimode
Product Family	LC Connectors, Adapters and Cable Assemblies
Product Name	LC
UPC	822350957229

Physical

Alignment Sleeve	Metal
Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Cable Size	8.00mm max.
Color - Resin	N/A
Ferrule Hole Size	127µm
Ferrule Material	Ceramic
Gender	Male
Material - Housing	PEI
Mounting Style	Adhesive
Net Weight	107.590/g
Ports	2
Wire/Cable Type	Round

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----