


# Large, Maxi Style Blade Fuse


ANX



## Mechanical Dimensions: Inches [mm]



## Retail Pack: Inches [mm]



## Part Numbers Information

| Amperage | Body Color | Bulk Part # | Retail Pack #<br>Blister Card | Pack<br>Size |
|----------|------------|-------------|-------------------------------|--------------|
| 20A      | Yellow     | ANX-20A     | ANX-20A-BP                    | 1            |
| 30A      | Green      | ANX-30A     | ANX-30A-BP                    | 1            |
| 40A      | Orange     | ANX-40A     | ANX-40A-BP                    | 1            |
| 50A      | Red        | ANX-50A     | ANX-50A-BP                    | 1            |
| 60A      | Blue       | ANX-60A     | ANX-60A-BP                    | 1            |
| 70A      | Tan        | ANX-70A     | ANX-70A-BP                    | 1            |
| 80A      | Clear      | ANX-80A     | ANX-80A-BP                    | 1            |
| 100A     | Violet     | ANX-100A    | -                             | -            |


## Electrical Specifications

|                     |                       |
|---------------------|-----------------------|
| Voltage Rating      | 32V DC                |
| Interrupting Rating | 1000A @ 32 VDC        |
| Testing             | SAE J1284, ISO 8820-3 |

## Material Specifications

|           |            |
|-----------|------------|
| Body      | PA 66      |
| Terminals | Zinc Alloy |

Time vs. Percent of Rated Current



| Rev | Date of issue | Revision Notes  | Designed | Approved |
|-----|---------------|-----------------|----------|----------|
| D   | 04-30-2024    | Initial Drawing | RC       | OF       |