

G

G

F

F

E

E

D

D

C





C

B

B

A

A



SPECIFICATIONS

Current Rating: 3Amps

Insulation Resistance: 1000MΩ Min

Contact Resistance: 20MΩ Max

Withstanding Voltage: AC 1000V

Operation Temperature: -40° to +105°

Contact Material: Copper Alloy

Standard: PA6T

Insrlator Material: Polyester (UL 94V-0)

Contact Plating: Gold Flash

Max. Processing Temp: 240° C for 30-60 seconds

(260° C for 5 seconds)



®
深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X.X : ±0.25 X.X° : ±1°

X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: HX PZ2.54-2x17P ZZ

SIZE A4 SCALE N:1 PROUT NO.

REV A UNIT mm PROJECT

PAGE 1/1

DRAW : 黄彬 2022/04/24 CHECKED: 张伟 2022/04/24 APPROVED: 罗小春 2022/04/24

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60

1

2

3

4

5

6

7

8

9