





SPECIFICATIONS

Contact Rating:	As per individual switch
Initial Contact Resistance:	Less than 20 milliohms
Insulation Resistance:	500VDC – 100 milliohms
Dielectric Strength:	500V AC for 1 minute between any terminal and frame
Operating Temperature:	-20°C to +70°C (-4°F to +158°F)
Soldering:	Auto 270 ± 5°C/3 seconds; Manual 350 ± 10° C/3 seconds
Life:	10,000 cycles minimum
Timing:	See individual specifications
	For special applications, contact factory


MATERIALS

Contact:	Silver plated copper alloy
----------	----------------------------



HOW TO ORDER




1201




Model No.	L
EG1201	4
EG1201A	5.5




PANEL MOUNT





Schematic




1205




Model No.	L
EG1205	4
EG1205A	5.5



P.C. MOUNTING




Schematic






SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

SERIES E G SWITCHES


SLIDE SWITCHES





1206






P.C. MOUNTING




Schematic




1213





P.C. MOUNTING




Schematic




1218




P.C. MOUNTING






Schematic




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.




1224






P.C. MOUNTING




Schematic





1247






P.C. MOUNTING




Schematic




1248



P.C. MOUNTING




Schematic




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

SERIES E G SWITCHES


SLIDE SWITCHES





1249



P.C. MOUNTING




Schematic




1253


Momentary Only




P.C. MOUNTING




Schematic




1257



P.C. MOUNTING



Schematic




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

SERIES E G SWITCHES




SLIDE SWITCHES





1270





P.C. MOUNTING






Schematic




1271



P.C. MOUNTING





Schematic





Model No.	L
EG1271	2
EG1271A	4.4




1302



P.C. MOUNTING



Schematic



Model No.	L
EG1302	6
EG1302A	9

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.