




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance:1000M Ω Min
Contact Resistance: 20M Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature:-40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Copper Alloy
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for5seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市韩下电子有限公司

UNLESS OTHEWIXE SPECIFIED TOLERANCE

X : ± 0.30 X $^{\circ}$: $\pm 5^{\circ}$
X. X : ± 0.25 X. X $^{\circ}$: $\pm 1^{\circ}$
X. XX : ± 0.20 X. XX $^{\circ}$: $\pm 0.5^{\circ}$

DRAWN NAME:

HX PZ2.54-2x15P ZZ

SIZE A4 SCALE N:1 PROUCT NO.
REV A UNIT mm PROJECT



PAGE 1/1

DRAW : 黄彬 2022/04/24 CHECKED: 张伟 2022/04/24 APPROVED: 罗小春 2022/04/24

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60