






Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS
Rated Current:1.0AMP
Contact Resistance:20mΩMax
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩMin
Operation Temperature:-40°c to +105°c

Contact Material:Phosphor Bronze
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature: 260°C±5° 5S



P = With Post

默认 = W/O Post

Ordering Information

PM 127 - * - N - S - * - ** - R - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
3-50Pin

Type
Z=直针
H=弯针
S=立插
P=卧插
W=反弯

Length
(mm)

Contact
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Plating

R=Reel
+Cap
(带帽+盖)

Post
(带柱)

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK	产品名称 TITLE	1.27双排 排母 贴片(塑高2.0)	版本 REV.	A
			X.X	±0.30	批准 APPROVAL	产品料号 PART NO.	PM127-2-N-S-2.0-XX(L2.3)	单位 UNITS	mm
			X.XX	±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection				
			Angle	±3.0°					