





SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Dimension antitheses list

ITEM	PA	A	PC	L
Standard	4.00	2.50	5.50	12.00
Alternate				

Ordering Information

PZ 127	- *	- N	- S	- C*	- **	- DP	- *	- P
No.of Rows 1=Single Row 2=Dual Row	No.of Pins 2-40Pin	Type 2=直插 3=弯插 4=贴片	(双排间距)	Contact G0:Gold G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flashy/Tin S1:Tin	Plating Flash	Double Plastic (双塑)	Packing R=Reel +Cap (编带+盖)	Post (带针)

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	1.27 双排 排针 卧贴 塑高2.5 (编带+盖)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	PZ127-2-N-WS-2.5-XX-R (L12.0)	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					
1	初版发行							