

規格型号:Specifications:

電気特性:Electrical:

1. 額定電流: Current Rating

1.5A/contact terminal

2. 額定電圧: Voltage Rating

30V DC

3. 接触抵抗:Contact Resistance

30 milliohms MAX

4. 耐電圧:Dielectnic Withstanding Voitage:

500 V AC AT Sea Levot

5. 抵抗:Lnsulation Resistance:

1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force

Mate force:3.57kgf(MAX)

Unmate force:1.02kgf(MIN)

原材料:Matatorial:

1. 塑膠:Housing:

Hing Temperature Tnermaplastics,

PBT/LCP White/Black

2. 端子:Contact:Copper Alloy C2680

3. 外殻:Shell: Copper Alloy SPCC

電鍍:Finish:

1. 端子:Contact: Plated Gold in Mating Area;

Tin On Solder Talls







端子鍍60U”(MIN)錫; 50U”(MIN)Ni;

測点鍍金Gold Flash/Copper tin

2. 外殻:Shell:

外殻四周鍍60U”(MIN)Ni, 60U”(MIN)Cu

Nickel Plating



RECOMMENDED P.C.B LAYOUT

		new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	041N-1WV821		UNLESS OTHERWISE SPECIFIED,TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3		
			MODEL NAME	041N-1WV821				
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.