



PANEL CUT-OUT



| X | L |
|---------|------|
| 0.8 | 24 |
| 1.0 | 24.6 |
| 1.2 | 25.2 |
| 1.6~2.0 | 26.2 |



Rating : 15A 125V AC UL cUL
 Insert And Extract Force: 1.36kgf~6.8kgf
 Terminal Strength: ≥60N
 Operating Life: ≥6000 cycles
 Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
 terminals to Base:3750V AC (50-60Hz)1min
 Leakage Current : 1mA
 Insulation Resistance: ≥100MΩ 500V DC
 Body Materil: NYLON 66 94V-2~

| 序号 | 名称 | 材料 | 处理 | 数量 | 备注 |
|----|------------------|--------|----|----|----|
| 1 | DB-F-M(H)-W109基座 | 环阻PA66 | 白色 | 1 | |
| 2 | DB-F-ML弹片 | 黄铜 | 镀锡 | 1 | |
| 3 | DB-F-MS(H) 弹片 | 黄铜 | 镀锡 | 2 | |

普通公差
COMMON TOLERANCE :

深圳市华灿天禄电子有限公司

| UP TO 5 | ±0.20 | 单 UNIT | mm | 投影 PROJECTED | ⊕ | 品名 PRODUCT NAME | Ac Outlet | 比例 SCALE | Free |
|---------------|----------------------|-------------|---------|---------------|---------|-----------------|-------------|----------|-------------|
| ABOVE 5 TO 30 | ±0.30 | 绘图 DRAWN BY | 金泽杰 | 核对 CHECKED BY | 张阜龙 | 型号 MODEL NO. | DB-F | | 版本号 VERSION |
| ABOVE 30 | ±0.50 | DRAWN BY | | CHECKED BY | | MODEL NO. | | | |
| REV. DATE | REVISION DESCRIPTION | ISSUE | ANGULAR | ±5° | 日期 DATE | 2024.7.15 | APPROVAL BY | 王天建 | PART NO. |