



General ordering data

Order No.	1956570000
Part designation	BLZP 5.00/05LR SN SW
Version	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 5, 180°, Box
EAN	4032248635382
Qty.	45 pc(s).

System parameters

Conductor connection system	Clamping yoke connection
Outgoing direction of conductor	180°
Pitch	5 mm
Pitch in inch	0.197 inch
No. of poles	5
No. of rows	1
Screwdriver blade	0.6 x 3.5
Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm
Clamping screw	M 2.5
Stripping length	7 mm
L1 in mm	20 mm
L1 in inch	0.787 inch
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	PBT
Colour	black
Insulating material group	IIIa
Flammability class UL 94	V-0
CTI	>= 200
Contact base material	Copper alloy
Contact surface	tinned

Connectable conductors

Clamping range, min.	0.13 mm ²
Clamping range, max.	4 mm ²
AWG, min.	26
AWG, max.	12
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	4 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	4 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.2 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	4 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	2.5 mm ²
Gauge to EN 60999 a x b; ø	2.8 mm x 2.4 mm

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	19 A
Rated current, max. No. pins (Tu=20°C)	15.5 A
Rated current, min. No. pins (Tu=40°C)	16 A
Rated current, max. No. pins (Tu=40°C)	13 A
Rated voltage for overvoltage class/pollution severity II/2	400 V
Rated voltage for overvoltage class/pollution severity III/2	320 V
Rated voltage for overvoltage class/pollution severity III/3	250 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	4 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	4 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	4 kV
Short-time withstand current resistance	3 x 1s with 120 A

CSA rating data

Rated voltage (Use group C)	50 V
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor (field wiring), min.	26
AWG conductor (field wiring), max.	12

UL 1059 rating data

Rated voltage (Use group C)	50 V
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor, min.	26
AWG conductor, max.	12

Approvals

Approvals institutes



Similar products

Order No.	Part designation	Version
1956370000	BLZP 5.00/02LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 2, 180°, Box
1956600000	BLZP 5.00/02LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 2, 180°, Box
1956360000	BLZP 5.00/03LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 3, 180°, Box
1956590000	BLZP 5.00/03LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 3, 180°, Box
1956350000	BLZP 5.00/04LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 4, 180°, Box
1956580000	BLZP 5.00/04LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 4, 180°, Box
1956340000	BLZP 5.00/05LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 5, 180°, Box
1956330000	BLZP 5.00/06LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 6, 180°, Box
1956560000	BLZP 5.00/06LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 6, 180°, Box
1956320000	BLZP 5.00/07LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 7, 180°, Box
1956550000	BLZP 5.00/07LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 7, 180°, Box
1956310000	BLZP 5.00/08LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 8, 180°, Box
1956540000	BLZP 5.00/08LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 8, 180°, Box

1956300000	BLZP 5.00/09LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 9, 180°, Box
1956530000	BLZP 5.00/09LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 9, 180°, Box
1956290000	BLZP 5.00/10LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 10, 180°, Box
1956520000	BLZP 5.00/10LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 10, 180°, Box
1956280000	BLZP 5.00/11LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 11, 180°, Box
1956510000	BLZP 5.00/11LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 11, 180°, Box
1956270000	BLZP 5.00/12LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 12, 180°, Box
1956500000	BLZP 5.00/12LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 12, 180°, Box
1956260000	BLZP 5.00/13LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 13, 180°, Box
1956490000	BLZP 5.00/13LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 13, 180°, Box
1956250000	BLZP 5.00/14LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 14, 180°, Box
1956480000	BLZP 5.00/14LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 14, 180°, Box
1956240000	BLZP 5.00/15LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 15, 180°, Box
1956470000	BLZP 5.00/15LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 15, 180°, Box
1956230000	BLZP 5.00/16LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 16, 180°, Box
1956460000	BLZP 5.00/16LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 16, 180°, Box
1956220000	BLZP 5.00/17LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 17, 180°, Box

1956450000	BLZP 5.00/17LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 17, 180°, Box
1956210000	BLZP 5.00/18LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 18, 180°, Box
1956440000	BLZP 5.00/18LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 18, 180°, Box
1956200000	BLZP 5.00/19LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 19, 180°, Box
1956430000	BLZP 5.00/19LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 19, 180°, Box
1956190000	BLZP 5.00/20LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 20, 180°, Box
1956420000	BLZP 5.00/20LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 20, 180°, Box
1956180000	BLZP 5.00/21LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 21, 180°, Box
1956410000	BLZP 5.00/21LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 21, 180°, Box
1956170000	BLZP 5.00/22LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 22, 180°, Box
1956400000	BLZP 5.00/22LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 22, 180°, Box
1956160000	BLZP 5.00/23LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 23, 180°, Box
1956390000	BLZP 5.00/23LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 23, 180°, Box
1956150000	BLZP 5.00/24LR SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 24, 180°, Box
1956380000	BLZP 5.00/24LR SN SW	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 4 mm ² , Pitch: 5.00 mm, No. of poles: 24, 180°, Box