



TOGGLE SWITCHES



✓ Active

TE CONNECTIVITY (TE)

A101TCQ04

Alcoswitch | A

5-1825136-4

TE Internal Number: 5-1825136-4

Alias ID: A101TCQ04

Always EU RoHS/ELV Compliant

Configuration (Pole-Throw) **Single Pole - Double Throw**

Bushing Thread Size **1/4-40**

Sealed **Yes**

Contact Base Material **Copper**

Contact Plating **Silver**

PRODUCT DRAWING

English

Product Drawings

GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITION FUNCTIONS (01 & 08)

PDF
English

Catalog Pages/Data Sheets

SWITCHES_CORE_PROGRAM_CATALOG

PDF
English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealed **Yes**

Toggle Style **Large with Bushing**

Switch Type **Toggle**

Toggle Actuation **Vertical**

Product Type **Switch**

Configuration Features

Configuration (Pole-Throw)

Single Pole - Double Throw

Operating Function

On On

Electrical Characteristics

Voltage Rating

20 VAC, 20 VDC

Contact Resistance (mΩ)

10

Dielectric Strength (VAC)	1000
Insulation Resistance (MΩ)	1000
Body Features	
Bushing Thread Size	1/4-40
Seal Type	Terminal Seal (Epoxy)
Bushing Style	Threaded
Actuator Finish	Nickel
Contact Features	
Contact Base Material	Copper
Contact Plating	Silver
Contact Current Rating (A)	5
Termination Features	
Termination Type	Printed Circuit
Mechanical Attachment	
Mounting Type	Through Hole
Housing Features	
Process Sealed	No
Dimensions	
Toggle Length	12.4 mm [.49 in]
Bushing Length (in)	.28
Industry Standards	
UL Flammability Rating	UL 94V-1
Product Compliance	
Statement of Compliance	
PDF	
VIEW ALL PRODUCT COMPLIANCE	