




Pushing Performance

R 15-GG mit M16



Part number	19 15 000 0401
Specification	R 15-GG mit M16
HARTING eCatalogue	https://b2b.harting.com/19150000401

Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Hood

Version

Locking type	Screw locking
Cable entry	1x M16

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate (PC)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	10
Net weight	16.28 g



Pushing Performance

Commercial data

Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors