

NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, straight with plastic cover, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 2 mm ... 10.5 mm, connection method: Crimp connection, series: NC, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240193

Commercial data

Item number	1592030
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB35
Product key	ABRIEA
GTIN	4046356190244
Weight per piece (including packing)	40.59 g
Weight per piece (excluding packing)	40.59 g
Customs tariff number	85389099
Country of origin	DE

NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

Technical data

Product properties

Product type	Circular connector (cable-side)
Series	NC
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn), plastic parts: SPS
Gasket and O-ring material	NBR

Connection data

Conductor connection

Connection method	Crimp connection
	Crimp connection
	Crimp connection

Connector

Type	straight with plastic cover
------	-----------------------------

Cable/line

External cable diameter	2 mm ... 10.5 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

NC-0000000KSFZ - Housing for circular connector



1592030

<https://www.phoenixcontact.com/us/products/1592030>

Classifications

ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5909118f-494f-4d48-ae6a-e7eac2c76b32