

Han-Eco 16B Outd.-HSM1-f. DL-M40-cov.-gl



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|-----------------------------|--|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Surface mounted housing |
| Description of hood/housing | With thermo-plastic cover With integrated cable gland |

Version

| | |
|-------------------------|------------------------------------|
| Size | 16 B |
| Version | Side entry |
| Number of cable entries | 1 |
| Cable entry | 1x M40 |
| Locking type | Double locking lever (on the hood) |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |
| Clamping range | 16 ... 28 mm |

Material properties

| | |
|-------------------------|--|
| Material (hood/housing) | Polyamide (PA) Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |



Material properties

| | |
|---|------------------------|
| Material (seal) | FPM |
| Colour (seal) | RAL 7001 (silver-grey) |
| Material flammability class acc. to UL 94 | V-0 |

Specifications and approvals

| | |
|----------------|---|
| Specifications | IEC 61984 EN 45545-2 Fire protection on railway vehicles |
| Approvals | CE |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140179400 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |