



MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
21EN51-R3 ★



21EN51-R3
M
DRAWING NUMBER
12
ISSUE
10/12
RELEASE NO. PR-2840
REPLACES
CHECK
REVISIONS
A CO 44351
S L B 14 SEPT 79
B CO47573 PART 4
R J H 8 AUG 80
C CO 48563-B
W J M 26 OCT 81
D CO68501
T S M 22 FEB 91
E CO71719
L J F 3 JAN 92
FO-52851-A
DRAWN
S L B 14 SEPT 79
CHECK
CEB
E O U T 79
CHECK

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X,X	0.4/016	X,X 0.8/03
TWO PLACES	X,XX	0.15/006	X,XX 0.38/015
THREE PLACES	X,XXX		X,XXX 0.13/005

DESIGN UNITS ☐ METRIC ☒ US CUSTOMARY

RAW MATERIAL-COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY
DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT 6 OZ MAX

CHARACTERISTICS

OPERATING FORCE ——— 3- 6 LB
FULL OVERTRAVEL FORCE ——— 17 LB MAX
RELEASE FORCE ——— 2 LB MIN
PRETRAVEL ——— .040 MAX
DIFFERENTIAL TRAVEL ——— .020 MAX
OVERTRAVEL ——— .250 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T (2)

LOAD

RES

IND

MOTOR

28 VDC

SEA LEVEL

50,000 FT.

4

2

4

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
- 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[21EN51-R3](#)